


KEOR SPX UPS



THE IDEAL SOLUTION FOR
ELECTRICAL NETWORK
DISTURBANCES

THE **GLOBAL SPECIALIST** IN ELECTRICAL AND DIGITAL
BUILDING INFRASTRUCTURES



KEOR SPX

Uninterruptible power supplies (UPS)



3 100 70

3 100 73

UPS for computers and audio and video equipment
Complete protection: discharge, overload, short-circuit, thermal protection
Supply button / LED indicators: provides a visual and audible indication of the UPS status
Reset push-button for the circuit-breaker: for resetting in the event that the overload protection is activated
Automatic start-up: when there is no mains supply or it is of poor quality, the UPS continues working using a battery and switches off if the network breaking time exceeds the back-up time

Pack	Cat. Nos.	Single-phase UPS				
		UPS with output sockets 2 Multistandard on 600-800VA UPS 4 Multistandard on 1000-1500-2000VA UPS German standard input plug Input voltage: 162-290 V - 50-60 Hz Output voltage: 220/230/240V Ambient operating temperature: 0 to 40°C Relative humidity: 0 to 90%				
1	3 100 70	Nominal power (VA) 600	Active power (W) 360	Back-up time (min) 10 to 15	Number of sockets 2	Communication ports -
1	3 100 71	800	480	10 to 15	2	-
1	3 100 72	1000	600	10 to 15	4	USB
1	3 100 73	1500	900	10 to 15	4	USB
1	3 100 74	2000	1200	10 to 15	4	USB

KEOR SPX

Uninterruptible power supplies (UPS)

	3 100 70	3 100 71	3 100 72	3 100 73	3 100 74
General characteristics					
Nominal power (VA)	600	800	1000	1500	2000
Active power (W)	360	480	600	900	1200
Technology	Line interactive VI				
Waveform	Pseudo-sinusoidal				
Input characteristics					
Input voltage	230 V				
Input frequency	50-60 Hz+/- 5Hz (autosensine)				
Input voltage range	162 V-290 V				
Output characteristics					
Output voltage	220 /230/240V				
Output frequency (nominal)	50/60 Hz +/-1%				
Batteries					
Number of batteries	1	1	2	2	2
Battery range type/voltage	12 V, 7 Ah	12 V, 9 Ah	12 V, 7 Ah	12 V, 9 Ah	12 V, 9 Ah
Communication and management					
Screen and signalling	One button and 1 LED for real-time control		One button and 3 LEDs for real-time control		
Remote control	Available				
Mechanical characteristics					
Dimensions H x W x D (mm)	142x101x279		182x130x320		
Net weight (kg)	4,2	4,9	8,2	10,4	10,6
Ambient conditions					
Ambient operating temperature (°C)	0 to 40°C				
Relative humidity (%)	0 to 90%				
Noise at 1 m (dB)	< 40				

NOTE: The stated back-up times in minutes are estimated and may vary according to the load characteristics, operating conditions and environment.

