

87045 LIMOGES Cedex

Telephone: (+33) 05 55 06 87 87 - Fax: (+33) 05 55 06 88 88

## Manual bypass Daker DK

3 109 53



TABLE OF CONTENTS	Page
General features	
2. Functional diagram	
3 Technical features	

## 1. GENERAL FEATURES

The manual maintenance bypass for Daker DK allows you to remove the UPS from its original installation without interrupting the power supply to the load, making it possible to carry out manoeuvres that need to be performed with the UPS switched off:

- Maintenance
- · Battery replacement
- · Uptime expansion
- Checking faults


Using the relative brackets it can be mounted to the back of Daker DK UPSs on Tower configurations and installations inside Rack cabinets. Using the cables provided, the Daker DK manual bypass is easy to connect to IEC inputs and outputs on the UPS.

The Daker DK Manual Bypass can only be used with Daker DK 1000, 2000 and 3000VA models.

Maintenance Bypass Distribution Box

## 2. FUNCTIONAL DIAGRAM

UPS mode



## 3. TECHNICAL FEATURES

General Features		
Transfer Time	4 ms	
Measurements H x L x D (mm)	440x88 (2U) x77	
Net Weight (kg)	3.5	

Environmental conditions	
Operating temperature (°C)	0 ÷ 40 °C
Degree of protection	IP21
Relative humidity (%)	20÷80 % non-condensing