

KEOR T 208V 40 – 50 - 60 kVA

3 102 97 – 3 102 98 – 3 102 99



1. GENERAL SPECIFICATIONS	1
1. ARCHITECTURE	1
2. REDUNDANCY	1
3. BYPASS	1
4. CONTROL AND MONITORING	1
2. TECHNICAL SPECIFICATIONS.....	3
1. GENERAL SPECIFICATIONS	3
2. INPUT	3
3. BYPASS	3
4. OUTPUT WITH MAINS (AC-AC)	3
5. OUTPUT ON BATTERY (DC-AC)	3
6. BATTERY	3
7. ENVIRONMENTAL SPECS	3
8. MECHANICAL AND MISCELLANEOUS.....	3

1. GENERAL SPECIFICATIONS

Legrand UPS model KEOR T 208V is an uninterruptible power source with 3-Level IGBT switching technology, high frequency PWM technology, Double Conversion On-line, solid neutral, with the possibility to have N+X on site modular redundancy up to total 6 units, Rated Power 40/50/60 kVA. Batteries are lead acid, sealed, free maintenance, valve regulated, and arranged, inside the UPS in dedicated Drawers or external battery cabinet. The architecture of this UPS is a Tower type.

1. Architecture

Legrand UPS model KEOR T 208V has stand-alone architecture. UPS is composed by following parts; - IGBT Rectifier/PFC - 3-Level IGBT Switching Technology - Digital Signal Processor (DSP) - 3.5" TFT Touch Panel - Automatic Bypass - Dual Input Bypass - Internal Manual Bypass - Standard Internal Backfeed Protection - Internal Battery Drawer Shelves. The UPS can be easily configured on site, by the authorized personnel, to operate in parallel. Also it is possible to arrange the dual bypass by removing bridge connection on each input phase. Legrand KEOR T 208V has 3-Level IGBT switching technology and there is no transformer in the unit. These provide high efficiency for the unit. Backfeed protection provides additional protection at the input in the event of bypass thyristors are short circuited. By using internal backfeed contactor in bypass line provides safety when fault situation occurs in static bypass line and prevents upstream energy to the input. The internal backfeed protection provides an easy on site installation without any additive cabling or special MCCB type in the upstream distribution panel.

2. Redundancy

The Redundancy of the UPS allows N+X redundant configurations. Up to 8 units of same size UPS can be connected in parallel.

3. Bypass

KEOR T 208V has internal both static bypass and mechanical (maintenance) bypass as standard. Addition to this input and bypass inputs can easily be separated to obtain dual input by removing the bridge on the connector.

4. Control and monitoring

KEOR T 208V is equipped with a touch screen graphic TFT display that provides information, measurements, statuses and alarms of the UPS in different languages. Below this display, there is a multicolor LED bar showing status of UPS.

- GREEN: Normal or ECO Mode Operation
- ORANGE: Bypass or Battery Operation
- RED: Load not Supplied

A dedicated software of remote monitoring and management, installed on a PC connected to the UPS, allows to check and set all working parameters of KEOR T 208V (the same functions available on the UPS control panel) and, furthermore, to schedule and program computer remote shutdown. Optional software (UPSMAN) or Net Interface card (CS141 SK) allow the multi server shutdown and UPS remote control on the LAN. Also, standard interface board comes with;

- RS232 Serial Communication Port
- Emergency Power Off (UPS OFF)
- Generator Contact (GEN ON)
- 4pcs programmable Dry Contact Information
- 2 contactor relays for Bypass and Battery
- ModBus (over RS485, with 2400 Baud Rate)

Standard Dry Contact Alarms are General Alarm, Bypass Active, Input Failure and Synchronization OK. Addition to these: High Temperature, Battery Test Failure, Output Failure alarms can be assigned to the contacts. Each alarm can be assigned to separate contact but also one alarm may be assigned to all contacts. KEOR T 208 front panel is controlled by DSP

KEOR T 208V 40 – 50 - 60 kVA**3 102 97 – 3 102 98 – 3 102 99**

microprocessor which works together with DSP microprocessors in rectifier and inverter; by display is possible to check all measurements, working parameters and status of the system. Here follow the measurements and working parameters available on the display:

RECTIFIER (INPUT)

Voltage (Vac), per phase
Current (Aac), per phase
DC BUS Voltage (\pm Vdc)

FREQUENCY

Input Frequency (Hz)
Output Frequency (Hz)

BATTERY

Voltage (\pm Vdc)
Current (\pm Adc)
Temperature
Autonomy (minute)

INVERTER (OUTPUT)

Voltage (Vac), per phase
Current (Aac), per phase
Apparent Power (kVA), per phase
Active Power (kW), per phase
Power Factor (load), per phase
Bypass Voltage, per phase
Load (%), per phase

The UPS allows also the following settings by **display**:

OUTPUT

Voltage (200/208/220)
Frequency (50Hz/60Hz)

BATTERY

Battery String
Battery Capacity

PARALLEL MODE

Parallel Mode
(Enable/Disable(Single))

UPS ID

Redundancy (+1, +2, ..., +5)
Operation Mode (Redundancy
Power Increase)

COMMAND MENU

Priority (Online (Inverter) /Green (Bypass))
Battery Test (KEOR T 208 tests the battery automatically once each 90 days)
Maintenance (Rectifier, Inverter, Bypass, Load Supply – YES/NO)

RELAY FUNCTIONS

Relay 1 (General Alarm as standard. Can be adjusted from 7 different alarms)

Relay 2 (Input Failure as standard. Can be adjusted from 7 different alarms)

Relay 3 (Battery Failure as standard. Can be adjusted from 7 different alarms)

Relay 4 (Output Failure as standard. Can be adjusted from 7 different alarms)

OPTIONS

Alarm Voice (Enable/Disable)
Key Voice (Enable/Disable)
Warning Window (Enable/Disable)

OTHER

Display Brightness (0 to 100)
Emergency Power Off (NC/NO)
Generator Mode (NC/NO)
ModBus ID
Time (hh:mm. Required for Event Log stamp)
Date (dd:mm:yyyy. Required for Event Log stamp)
Language (English)

Legrand KEOR T 208 displays up to 500 last events. Events are stored in EEPROM using FIFO method. Order number of last occurred event is 001 and the last event in the list is erased when there are 500 events.

The UPS KEOR T 208 has the CE Mark accordingly with the EU Directives 73/23, 93/68, 89/336, 92/31, 93/68 and it complies with following standards:

- EN 62040-1 "General rules for electric safety"
- EN 62040-2 "Electromagnetic compatibility and immunity (EMC)"
- EN 62040-3 "Performances and testing rules"

KEOR T 208V 40 – 50 - 60 kVA

3 102 97 – 3 102 98 – 3 102 99

2. TECHNICAL SPECIFICATIONS

1. General specifications

Model	40	50	60
UPS Topology	On line double conversion VFI SS 111		
Architecture of the UPS	Stand alone, transformerless, On-Site Paralleling		
In/Out phase Configuration	Three phase-Three phase		
Neutral	Neutral Passing through		
Switching Technology	3-Level IGBT		
Backfeed Protection	Internal, standard		
Output wave form on mains operation	Sinusoidal		
Output wave form on battery operation	Sinusoidal		
Standards	EN 62040-1, EN 62040-2, EN 62040-3		

2. Input

Nominal Voltage	208V 3ph+N+PE
Voltage Range	176 – 239V Ph-Ph full load 108 - 239 V Ph-Ph half load
Frequency	45 - 65Hz
THDin	< 5% at full load
Power Factor	> 0.99

3. Bypass

Nominal Voltage	208V 3ph+N+PE
Voltage Range	200/208/220V -18% +15% (adjustable)
Frequency	47-53Hz or 57-63Hz (adjustable)
Bypass Type	Static and Electro-mechanic
Transfer Time	Zero
Manual Bypass	Built-in

4. Output with mains (AC-AC)

Nominal Voltage	200, 208, 220V 3ph+N+PE
Nominal Power (KVA)	40 50 60
Active Power (KW)	36 45 54
Voltage variation (static)	± 1%
THDv on nominal power (linear load)	< 2%
THDv on nominal power (non-linear load)	< 4%
Frequency	50 Hz or 60 Hz (selectable)
Frequency tolerance	± 0,1% Synchronized with input frequency
Current Crest Factor	2.5:1 accordingly to IEC 62040-3
Overload capability:	
10 min	125% load with no bypass
60 sec	150% load with no bypass

5. Output on battery (DC-AC)

Model	40	50	60
Nominal Voltage	200, 208, 220 3ph+N+PE		
Nominal Power (KVA)	40	50	60
Active Power (KW)	36	45	54
Voltage variation (static)	± 1%		
THDv on nominal power (linear load)	< 2%		
THDv on nominal power (non-linear load)	< 4%		
Frequency	50 Hz or 60 Hz (selectable)		
Frequency tolerance	± 0,01% free run		
Current Crest Factor	2.5:1 accordingly to IEC 62040-3		
Overload capability:			
10 min	125% load with no Bypass		
60 sec	150% load with no Bypass		

6. Battery

Type	Lead Acid, sealed, free maintenance VRLA
Unit Capacity	7 or 9 Ah (12V)
Nominal UPS Battery Voltage	±204 Vdc (max ±216 Vdc)
Nominal n. of possible internal battery	0
Battery charger type	IGBT Rectifier also charges batteries
Charging Cycle	Intelligent with boost charge and advanced management"
Max Charging Current without derating	6A 7A 8A

7. Environmental specs

Noise level @ 1m (50% load)	< 58dBA
Operating temperature range	from 0°C to +40°C
Stock temperature range	from -20°C to +50°C
Humidity range	20-95% not condensing
Protection degree	IP20

8. Mechanical and miscellaneous

Net Weight without batteries ¹	317Kg 348Kg 365Kg
Dimensions (HxW xD)	1650*600*980mm 1650*793*800mm
Colour	Enclosure: RAL 7016 Front Door Metal: RAL 9005
Communication Interface	1 serial port RS232, 1 RS485, 1 smart port for internal SNMP, 4 Dry Contacts, 1 EPO, 1 GENSET
Input/Output connections	3Ph + N + PE

¹ The weigh depends by the number of the installed batteries accordingly with the required autonomy.