

UPS Technical Specification

Declaration of additional requirements in accordance with IEC 62040-4

DAKER DK Plus		
Subclause IEC 62040-4	Declared environmental aspect	LEGRAND's declared value
5.2.2	Location of manufacturing plant(s)	China
	Environmental management system (certification status and name of system)	ISO 14001
5.2.3	Model	3 101 73
	Power, rated – apparent – active	5000 VA 5000 W
	Representative UPS	Yes
	Range of UPS covered by representative UPS	DAKER DK Plus 5-6 kVA
	UPS configuration	Single UPS with bypass
	Performance classification	VFI-SS-111
	Dimensions (height × width × depth)	440 x 176 x 680 mm
	Mass	27 kg
	Mass of batteries if integrated	29 kg
	Battery technology	Lead-acid batteries (VRLA)
	Product packaging (mass, material)	Total weight of Reference Product: 59244 g (all packaging included) Packaging as % of weight: - Paper: 4.6% - PS: 0.7% - PE: 0.2%
Group packaging, if applicable (mass, material)	-	
Transportation packaging, if applicable (mass, material)	-	
5.2.4	Substances – Criterion 1	<ul style="list-style-type: none"> - Lead alloyed (CAS 7439-92-1) in the metals and batteries - Lead titanium zirconium oxide (CAS 12626-81-2) in piezoelectric electronic components - Diboron trioxide (CAS 1303-86-2) in some electronic components - Lead not alloyed (CAS 7439-92-1) in some electronic components

UPS Technical Specification

Declaration of additional requirements in accordance with IEC 62040-4

Subclause IEC 62040-4	Declared environmental aspect	LEGRAND's declared value
5.2.5	UPS Efficiency	Up to 94 %
	Acoustic Noise	< 50 dBA at 1m
5.2.6	End of life information	<ul style="list-style-type: none">- lead-acid batteries: 29000 g- printed circuit boards if larger than 10 cm²: 9204 g- plastic containing regulated flame retardants- electrolytic capacitors of height > 25 mm and diameter > 25 mm or proportionately similar volume

UPS Technical Specification

Declaration of additional requirements in accordance with IEC 62040-4

DAKER DK Plus		
Subclause IEC 62040-4	Declared environmental aspect	LEGRAND's declared value
5.3.2.2	Recyclable material, (percentage by mass, calculation method) – in product – in packaging	Calculated using the method described in technical report IEC/TR 62635, the recyclability rate of the product is estimated at 68 %. This value is based on data collected from a technological channel operating on an industrial basis. It does not pre-validate the effective use of this channel for the end of life of this product. Separated into: - plastic materials (excluding packaging): 0 % - metal materials (excluding packaging): 29 % - other materials (excluding packaging): 34 % - packaging (all types of materials): 5 %
5.3.2.3	Life cycle assessment	Global warming Total for Life Cycle: 1.34E+04 kgCO2 eq. Raw material and manufacture: 3.82E+02 - 3% Distribution: 2.30E+00 - < 1% Installation: 2.32E-01 - < 1% Use: 1.35E+04 - 97% End of life: 5.78E+00 - < 1% <i>for more details, check the Product Environmental Profile</i>